



PICQ.E175157 Measuring, Testing and Signal Generation Equipment

[Page Bottom](#)

Measuring, Testing and Signal Generation Equipment

[See General Information for Measuring, Testing and Signal Generation Equipment](#)

MULTI-CONTACT ESSEN GMBH

E175157

HOEVELSTRASSE 214
45326 ESSEN, GERMANY

Adapters, Models HVA-4, XAA-4.

Models XDS-BS/58, XDS-BS/SIL.

Back probe pin, Model KSA-BPP.

BNC adapters, Model BB120.

Models TKBA, XF-BB/4, XF-SS/4, XM-BB/4, XM-SS/4.

Coax splitters, Models XLAF-4805, XLAM-480.

Models XLAM-414/SC, XLAM-414/SC/SIL, XLAM-446/SC, XLAM-446/SC/SIL, XLAM-484/SC, XLAM-484/SC/SIL.

Dolphin clips, Models XDK-1033, XDK-1033P, XDK-1033P/I.

Fused probes, Models Grip-DI, TAST-D, XPS-180A, XPS-180.

Grabbers, Models Microgrip-XB, Minigrip-XA, -XB, -XC, -XCI, TGA, XKK-200.

Grips, Models ZGA, ZGB/100, ZGC, ZGCI.

Ground leads, Models SLK205-K, -K/SIL, -L, -L/SIL, STL120, XALS-4/2A.

High V test pin, Model HVA-2.

Hook clips, Models HC120.

Models SKPS-4/A, SKPS-4.

Oscilloscope probes, Models Iso probe 1:1, -10:1.

Models GB200, GH200, GM200, IP2-40, IP2-150, IP2-200, IP2-250, IP2-300, IP2-450, IP2W-150, RLW/Flex, TL200, VP100, VP-120, VP200, VP201, VP210, VP212, VP220, VP250.

Oscilloscope probe sets, Models AS200-G, AS200R, Isoprobe II 1.1 40 Mhz, Isoprobe II 10:1 - 150 Mhz - 250 Mhz - 450 Mhz - 200 Mhz - 300 Mhz, Isoprobes III 10:1 HS, Isoprobes III 10:1 ECO, Isoprobes III 10:1 HF, Isoprobes III 100:1, RS200, TLS200, VPS100, VPS121, VPS200G, VPS200R, VPS-201, VPS-250.

Probe accessories, Models AB200, AC200, BT200, GS200, Grip F, HC200, PB200, PT200.

Test leads, Models STL90, STL120, XALF, XALS, XKF-402, -414, XKS-402, -414, XLAF-414, -480, XLAM-414, -14/SIL, -480/SIL, XLSK-5, XLSS/SIL, -58, XMF-402, -414, -482, -484, XMS-402, -414, -480/414, -480/480, -482, -484, XPF-402/2G, -402/4, -414, -408/2G, -482/4, -484, XPS-402/2G, -402/4, -414, -480/2G, -482/4XPS-484, XVF-446, -448, XVS-446, -448.

Model VPX40

Models SLK410-SI/SIL, SLK425-BFT/N, SLK425-SI, SLK425-SI/SIL, SLK425-T/N, SLK606-AR/BGG, SLK4075-E/N, SLK410-E/SIL, SLK425-E, SLK425-E/N, SLK606-AR/BGG/SIL, SLK606-AR/BGW, SLK606-AR/BGW/SIL, SLK606-AR/BWW, SLK606-AR/BWW/SIL, SLK606-AR/FMA/BG, SLK606-AR/FMA/BG/SIL, SLK610-AR/BGG, SLK610-AR/BGG/SIL, SLK610-AR/BGW, SLK610-AR/BGW/SIL, SLK610-AR/BWW, SLK610-AR/BWW/SIL, SLK616-AR/BGG, SLK616-AR/BGG/SIL, SLK616-AR/BGW, SLK616-AR/BGW/SIL, SLK616-AR/BWW, SLK616-AR/BWW/SIL, SLK625-AR/BGG, SLK625-AR/BGG/SIL, SLK625-AR/BGW, SLK625-AR/BGW/SIL, SLK625-AR/BWW, SLK625-AR/BWW/SIL, XKS-414, XMF-419, XMS-419, XMT-414, XMT-419, XMT-484, XPZ-4AKO, XPZ-4AZW, XPZ-4WKO, XPZ-4WZW, XPZ-BM, XSPS-200, XSPS200/A, XSPS-280, XSPS-280A.

Test pins, Models KSA-2, -4/19, -4/19S.

Test prod, Model XPP-80/XX, where XX may be any alphanumeric combination. The suffixes represent the probe tip style.

4mm safety probes, Models Grip-A, -B/50/100/200, -Ci, HP-150A, -150B, PP-115/2N, -115/4, XKK-1001.

[Last Updated on 2007-04-30](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2007 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

